

# Compression Terminal

By Burndy  
Catalog # YAV2402M10

HYLUG™ Copper tubing Compression terminals,240 mm<sup>2</sup>,M10 Stud, 2 Holes,Tin Plated.



## Application

Metric Wire Termination

## General

Connector Type	METRIC
Die Index	20
Finish Type	Tin-Plated
Material	COPPER
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638125
UPC 12 Digit	7818106381255

## Dimensions

Dimension - B Length inch	32.3 in
Dimension - Bolt Hole Size inch	0.41 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	117.6 mm
Dimension - Length Overall inch	4.63 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.27 in
Dimension - Stud Size fraction	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Material	COPPER
Conductor Size	240 mm <sup>2</sup>
Conductor Type	CLASS 2

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	10
Minimum Pack Quantity	10

## Product Assets

[3D Models - YAV2402M10\\_MODEL-STEP](#)  
[3D Models - YAV2402M10\\_MODEL-IGES](#)  
[3D Models - YAV2402M10\\_MODEL-PDF](#)  
[Sales Drawings - 50025887](#)

