



YAV2402M20, Compression Terminal

By Burndy
Catalog # [YAV2402M20](#)

Hylug Copper tubing Compression terminals, 240 mm², M20 Stud, 2 Holes, Tin Plated.



Application

Metric Wire Termination

General

Catalog Number	YAV2402M20
Connector Type	METRIC
Die Index	20
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638132
UPC 12 Digit	7818106381322

Dimensions

Dimension - B Length inch	32.3 in
Dimension - Bolt Size fraction	7/8
Dimension - Bolt Size inch	0.88
Dimension - Hole Size fraction	7/8
Dimension - Hole Size inch	0.94
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	141 mm
Dimension - Length Overall inch	5.61 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.30 in
Dimension - Stud Size fraction	7/8
Dimension - Z (inch)	0.89 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Material	COPPER
Conductor Size	240 mm ²
Conductor Type	CLASS 2

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5
Minimum Pack Quantity	5
Pallet Quantity	4800

Product Assets

- [3D Models - YAV2402M20_MODEL-PDF](#)
- [3D Models - YAV2402M20_MODEL-STEP](#)
- [3D Models - YAV2402M20_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
- [Sales Drawings - 50025887](#)
- [Specifications - YAV2402M20](#)