

Compression Terminal

By Burndy
Catalog # [YAV240FM10](#)

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 240 mm, 10 mm Stud, 2.87 IN L, Compression, 20 Index, 33 mm Strip Length.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	20
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810322376
UPC 12 Digit	7818103223766

Dimensions

Dimension - B Length inch	1.27 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	72.9 mm
Dimension - Length Overall inch	2.87 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.30 in
Dimension - Stud Size fraction	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Flex G Size	240
Conductor - Copper Flex H Size	240
Conductor - Copper Flex I Size	240
Conductor - Copper Flex K Size	240
Conductor - Copper Flex M Size	240
Conductor - Material	COPPER
Conductor Size	240 mm ²
Conductor Type	CLASS 5

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5
Minimum Pack Quantity	5

Product Assets

[3D Models - YAV240FM10_MODEL-IGES](#)
[3D Models - YAV240FM10_MODEL-PDF](#)
[3D Models - YAV240FM10_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025612](#)

