



YAV240M12, Compression Terminal

By Burndy

Catalog # [YAV240M12](#)

Non insulated Cu tubular terminals, Metric, 1 Hole/W/insp W,
240mm Class2, 1/2" stud, Tin - Electro Plated, 20 Index.



Application

Metric Wire Termination

General

Catalog Number	YAV240M12
Connector Type	METRIC
Die Index	20
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810285749
UPC 12 Digit	7818102857499

Dimensions

Dimension - B Length inch	1.27 in
Dimension - Bolt Hole Size inch	0.53 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - D inch	1.14 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	80.2 mm
Dimension - Length Overall inch	3.16 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.27 in
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	500
Conductor - Material	COPPER
Conductor Size	240 mm ²
Conductor Type	CLASS 2

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	5
Minimum Pack Quantity	5

Product Assets

[3D Models - YAV240M12_MODEL-IGES](#)
[3D Models - YAV240M12_MODEL-PDF](#)
[3D Models - YAV240M12_MODEL-STEP](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
[Sales Drawings - 50025521](#)
[Specifications - YAV240M12](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAV240M12-SPEC-EN | REV 8/2024