

# Compression Terminal

By Burndy  
Catalog # [YAV240M20](#)

Copper Tubing Terminal, 1 Hole W/insp window, 240 mm Class 2, 20 Index, 20 mm Stud.



## Application

Metric Wire Termination

## General

Connector Type	METRIC
Die Index	20
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810322468
UPC 12 Digit	7818103224688

## Dimensions

Dimension - B Length inch	1.27 in
Dimension - Bolt Size fraction	7/8
Dimension - Bolt Size inch	0.88
Dimension - D inch	1.72 in
Dimension - Hole Size fraction	7/8
Dimension - Hole Size inch	0.94
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	96.6 mm
Dimension - Length Overall inch	3.80 in
Dimension - N inch	0.88 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1.27 in
Dimension - Stud Size fraction	7/8
Dimension - Z inch	0.89 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Material	COPPER
Conductor Size	240 mm <sup>2</sup>
Conductor Type	CLASS 2

## Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

## Logistics

Carton Quantity	5
Minimum Pack Quantity	5

## Product Assets

[3D Models - YAV240M20\\_MODEL-PDF](#)  
[3D Models - YAV240M20\\_MODEL-IGES](#)  
[3D Models - YAV240M20\\_MODEL-STEP](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50025521](#)

