

YAV252M6, Compression Terminal

By Burndy

Catalog # [YAV252M6](#)

HYLUG™ Copper tubing Compression terminals, 25 mm², M6 Stud, 2 Holes, Tin Plated.



Application

Metric Wire Termination

General

Catalog Number	YAV252M6
Connector Type	METRIC
Die Index	9
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637777
UPC 12 Digit	7818106377777

Dimensions

Dimension - B Length inch	12.7 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.20 in
Dimension - Pad Width inch	12.7 in
Dimension - Strip Length inch	0.51 in
Dimension - Stud Size fraction	1/4
Dimension - Z (inch)	0.33 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Material	COPPER
Conductor Size	25 mm ²
Conductor Type	CLASS 2

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	50
-----------------------	----

Product Assets

[3D Models - YAV252M6_MODEL-IGES](#)

[3D Models - YAV252M6_MODEL-PDF](#)

[3D Models - YAV252M6_MODEL-STEP](#)

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)

[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)

[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)

[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)

[Sales Drawings - 50025887](#)

[Specifications - YAV252M6](#)