

# Compression Terminal

By Burndy  
Catalog # [YAV25L2NT14FX90](#)

Copper Compression Lug, Narrow Tongue, 2 Holes W/  
Inspection Window, 1/0 AWG, 1/4" Stud, 12 index, Pink, Tin  
plated, 90 Degree



## Application

Wire Termination

## General

Color	Pink
Color Code	Pink
Connector Type	STANDARD BARREL
Construction Material - Main	Copper
Die Index	12
EU RoHS Indicator	Contact Manufacturer
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Number of Holes	2
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Narrow Tongue
UPC	781810660843

## Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.69 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	42 mm
Dimension - Length Overall inch	1.66 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.64 in
Dimension - Strip Length inch	11/16 in
Dimension - Stud Size fraction	1/4

## Conductor Related

Conductor - Copper DLO Size	1/0 AWG
Conductor - Copper DLO Size Range	1/0 AWG
Conductor - Copper Flex G Size	"1/0 AWG"
Conductor - Copper Flex G Size Range	1/0 AWG
Conductor - Copper Flex H Size	"1/0 AWG"
Conductor - Copper Flex H Size Range	1/0 AWG
Conductor - Copper Flex I Size	"1/0 AWG"
Conductor - Copper Flex I Size Range	1/0 AWG
Conductor - Copper Flex K Size	"1/0 AWG"
Conductor - Copper Flex K Size Range	1/0 AWG
Conductor - Copper Flex M Size	"1/0 AWG"
Conductor - Copper Str Compact Size	"1/0 AWG"
Conductor - Copper Str Navy Size	100
Conductor - Copper Str Navy Size Range	100 (61) Navy
Conductor - Copper Str Size	"1/0 AWG"
Conductor - Copper Str Size Range	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE/FLEX
Wire Size	1/0 AWG

## Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Dimension - Stud Size fraction 1/4  
Dimension - Stud Size inch 1/4 in  
Physical Attribute - Tongue Angle 90 Degree

Carton Quantity 25  
Minimum Pack Quantity 1  
Pallet Quantity 24000

### Electrical Ratings

Voltage - Maximum 35000  
Voltage Rating 35 kV

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - 50035189](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-YAV25L2NT14FX90-SPEC-EN | REV 5/2024