



YAV26L22, Ring Terminal, 2/0 AWG, 1-Hole, 3/4" Stud

By Burndy
Catalog # [YAV26L22](#)

Seamless Uninsulated Ring, 2/0 AWG, 1-Hole, 3/4" Stud, Double Thick Tongue, Standard Barrel, Tin Plated

Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	2/0 AWG
Conductor - Copper Str Aircraft Size Range	AN 00
Conductor - Copper Str Aircraft Size	AN 00
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	2/0 AWG
Conductor - Copper Str Size	2/0 AWG

Configuration

Physical Attribute - Number of Holes	1
Connector Type	Ring Terminal



Dimensions

Dimension - Pad Width inch	1.12 in
Dimension - Bolt Hole Size inch	0.91 in
Package Height	0.000 in
Dimension - Bolt Size fraction	3/4
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	3/4 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Z inch	0.79 in
Dimension - B Length inch	0.78 in
Dimension - D inch	1.29 in
Dimension - N inch	0.5 in
Dimension - Hole Size mm	20 mm
Dimension - Length Overall inch	2.66 in
Dimension - Stud Size inch	3/4 in

General

Material Composition	• DLP Copper • Tin Plating
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Yes
Product Family	COMPRESSION
Trade Name	HYLUG™
Physical Attribute - Tongue Type	Ring
Die Index	44
Product Type	Terminal
UPC	781810025703
Type	Ring Tongue
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810025703

Logistics

Minimum Pack Quantity	100
Pallet Quantity	29600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand