

Compression Terminal

By Burndy
Catalog # [YAV26L2TC12E1FX](#)

2/0 Flex G,H,I,K,M,DLO, 2/0 AWG CU, Two Hole, 1/2 Stud Size, 1 Hole Spacing, Standard Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 13 Die Index.



Application

Wire Termination

General

Color Code	Black
Connector Type	STANDARD BARREL
Die Index	13
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Yes
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810021774
UPC 12 Digit	7818100217744

Dimensions

Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	86 mm
Dimension - Length Overall inch	3.37 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.63 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	13/16 in
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.56 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper DLO Size	2/0 AWG
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	"2/0 AWG"
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Str Compact Size	"2/0 AWG"
Conductor - Copper Str Navy Size	125
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Str Size Range	2/0 AWG
Conductor - CopperWeld Str Size	2/0 F AWG;2/0 G AWG;2/0 J AWG;2/0 K AWG;2/0 V AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE/FLEX
Wire Size	2/0 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	18500

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SE..208119-01](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAV26L2TC12E1FX-SPEC-EN | REV 5/2024