



YAV26LTC12FX90, Compression Terminal, 2/0 Flex G,H,I,K,M, DLO, 2/0 AWG, Cu, 1-Hole, 1/2" Stud, Standard Barrel, 90 Degree

By Burndy
Catalog # YAV26LTC12FX90



2/0 Flex G,H,I,K,M,DLO, 2/0 AWG CU, One Hole, 1/2 Stud Size, Standard Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 13 Die Index.

Application

Wire Termination

General

| | |
|--------------------------------------|-----------------------------|
| Catalog Number | YAV26LTC12FX90 |
| Color Code | Black |
| Connector Type | STANDARD BARREL |
| Die Index | 13 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Finish Type | Tin-Plated |
| Material | COPPER |
| Physical Attribute - Number of Holes | 1 |
| Physical Attribute - Tongue Type | Standard |
| Plated | Yes |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810035818 |
| UPC 12 Digit | 7818100358188 |

Dimensions

| | |
|-----------------------------------|-----------|
| Dimension - B Length inch | 0.81 in |
| Dimension - Bolt Hole Size inch | 0.53 in |
| Dimension - Bolt Size fraction | 1/2 |
| Dimension - Bolt Size inch | 0.5 |
| Dimension - Hole Size fraction | 1/2 |
| Dimension - Hole Size inch | 0.53 |
| Dimension - Hole Size mm | 13.5 mm |
| Dimension - L Length Overall mm | 38 mm |
| Dimension - Length Overall inch | 1.51 in |
| Dimension - N inch | 0.53 in |
| Dimension - Outside Diameter inch | 0.63 in |
| Dimension - Pad Width inch | 0.93 in |
| Dimension - Strip Length inch | 13/16 |
| Dimension - Stud Size fraction | 1/2 |
| Dimension - Z (inch) | 0.55 in |
| Physical Attribute - Tongue Angle | 90 Degree |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Conductor Related

| | |
|--------------------------------|---------------------------|
| Conductor - Copper DLO Size | 2/0 AWG |
| Conductor - Copper DLO Size | 2/0 AWG |
| Range | |
| Conductor - Copper Flex G Size | "2/0 AWG" |
| Conductor - Copper Flex G Size | 2/0 AWG |
| Range | |
| Conductor - Copper Flex H Size | "2/0 AWG" |
| Conductor - Copper Flex H Size | 2/0 AWG |
| Range | |
| Conductor - Copper Flex I Size | "2/0 AWG" |
| Conductor - Copper Flex I Size | 2/0 AWG |
| Range | |
| Conductor - Copper Flex K Size | "2/0 AWG" |
| Conductor - Copper Flex K Size | 2/0 AWG |
| Range | |
| Conductor - Copper Flex M | "2/0 AWG" |
| Size | |
| Conductor - Copper Str | "2/0 AWG" |
| Compact Size | |
| Conductor - Copper Str Navy | 125 |
| Size | |
| Conductor - Copper Str Navy | 125 (61) Navy |
| Size Range | |
| Conductor - Copper Str Size | "2/0 AWG" |
| Conductor - Copper Str Size | 2/0 AWG |
| Range | |
| Conductor - CopperWeld Str | 2/0 F AWG;2/0 G AWG;2/0 J |
| Size | AWG;2/0 K AWG;2/0 V AWG |
| Conductor - Material | COPPER |
| Conductor Size | 2/0 AWG |
| Conductor Type | CODE/FLEX |
| Wire Size | 2/0 AWG |

Certifications And Compliance

| | |
|-------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - RoHS Compliance | CM |
| Status | |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 25 |
| Minimum Pack Quantity | 25 |
| Pallet Quantity | 24000 |

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..208001-01](#)
[Specifications - YAV26LTC12FX90](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand