



YAV26LTC14FX90, Compression Terminal, 2/0 Flex G,H,I,K,M, DLO, 2/0 AWG, Cu, 1-Hole, 1/4" Stud, Standard Barrel ,90 Degree

By Burndy

Catalog # YAV26LTC14FX90



2/0 Flex G,H,I,K,M,DLO, 2/0 AWG CU, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 13 Die Index.

Application

Wire Termination

General

Catalog Number	YAV26LTC14FX90
Color Code	Black
Connector Type	STANDARD BARREL
Die Index	13
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810053188
UPC 12 Digit	7818100531888

Dimensions

Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.07 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.63 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	13/16
Dimension - Stud Size fraction	1/4
Dimension - Z (inch)	0.33 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	2/0 AWG
Conductor - Copper DLO Size	2/0 AWG
Range	
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper Flex G Size	2/0 AWG
Range	
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex H Size	2/0 AWG
Range	
Conductor - Copper Flex I Size	"2/0 AWG"
Conductor - Copper Flex I Size	2/0 AWG
Range	
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex K Size	2/0 AWG
Range	
Conductor - Copper Flex M	"2/0 AWG"
Size	
Conductor - Copper Str	"2/0 AWG"
Compact Size	
Conductor - Copper Str Navy	125
Size	
Conductor - Copper Str Navy	125 (61) Navy
Size Range	
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Str Size	2/0 AWG
Range	
Conductor - CopperWeld Str	2/0 F AWG;2/0 G AWG;2/0 J
Size	AWG;2/0 K AWG;2/0 V AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE/FLEX
Wire Size	2/0 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	24000

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..208001-01](#)
[Specifications - YAV26LTC14FX90](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAV26LTC14FX90-SPEC-EN | REV 8/2024