



YAV26LTC38FX, Cu Compression, 1-Hole, 3/8" Stud, Standard Barrel, 2/0 Flex

By Burndy

Catalog # [YAV26LTC38FX](#)

2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, CU, 1 Hole, 3/8 Stud, Standard Barrel, Inspection Window

Features

- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding
- For applications greater than 2000 Volts consult cable manufacturer for voltage stress relief instructions

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Range	
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Flex I Size	2/0 AWG
Range	
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper DLO Size	2/0 AWG
Range	
Conductor - Copper Str	"2/0 AWG"
Compact Size	
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex G Size	2/0 AWG
Range	
Conductor - Copper Str Navy	125 (61) Navy
Size Range	



Conductor - Copper Str Navy	125
Size	
Conductor - CopperWeld Str	• 2/0 F AWG
Size	• 2/0 G AWG
	• 2/0 J AWG
	• 2/0 K AWG
	• 2/0 V AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	2/0 AWG
Range	
Conductor - Copper Flex H Size	2/0 AWG
Range	
Conductor - Copper Flex I Size	"2/0 AWG"

Configuration

Physical Attribute - Number of	1
Holes	
Number of Pad Holes	1
Connector Type	STANDARD BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.93 in
Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - Hole Size fraction	3/8
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	54 mm
mm	
Dimension - Outside Diameter	0.63 in
inch	
Dimension - Hole Size mm	10.4 mm
Dimension - Hole Size inch	0.41
Dimension - Strip Length inch	13/16
Dimension - Stud Size inch	3/8
Dimension - Stud Size fraction	3/8
Dimension - Bolt Hole Size inch	0.40 in
Dimension - Bolt Size fraction	3/8
Physical Attribute - Tongue	Straight
Angle	
Dimension - Z inch	0.42 in

Dimension - B Length inch	0.81 in	Material	Copper
Dimension - N inch	0.41 in	Plating Type	Tin
Dimension - Bolt Size inch	0.38	Finish Type	Tin-Plated
Dimension - Length Overall inch	2.11 in	UPC 12 Digit	781810021989
		UPC 14 Digit GTIN	00781810021989
General		Logistics	
Trade Name	HYLUG™	Minimum Pack Quantity	1
Die Index	13	Pallet Quantity	29000
Feature - Barrel Type	Standard	Carton Quantity	100
Feature - Barrel Style	Chamfered		
Plated	Yes	Product Assets	
Color Code	Black	Catalog [English]	
Sub Brand	HYLUG	Installation Manual [English]	
UPC	781810021989	Installation Manual [English]	
Type	Standard Barrel, Tin Plated		



A Hubbell brand