



YAV26LTC516FX, Cu Compression, 1-Hole, 5/16" Stud, Standard Barrel, 2/0 Flex

By Burndy
Catalog # [YAV26LTC516FX](#)



2/0 Flex G,H,I,K,M,DLO, 2/0 AWG CU, One Hole, 5/16 Stud Size, Standard Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 13 Die Index.

Application

Wire Termination

General

Color Code	Black
Connector Type	STANDARD BARREL
Die Index	13
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810021996
UPC 12 Digit	7818100219966

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.98 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.63 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	13/16
Dimension - Stud Size fraction	5/16
Dimension - Stud Size inch	5/16

Conductor Related

Conductor - Copper DLO Size	2/0 AWG
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Flex G Size	"2/0 AWG"
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Flex H Size	"2/0 AWG"
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	"2/0 AWG"
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex K Size	"2/0 AWG"
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex M Size	"2/0 AWG"
Conductor - Copper Str Compact Size	"2/0 AWG"
Conductor - Copper Str Navy Size	125
Conductor - Copper Str Navy Size Range	125 (61) Navy
Conductor - Copper Str Size	"2/0 AWG"
Conductor - Copper Str Size Range	2/0 AWG
Conductor - CopperWeld Str Size	2/0 F AWG;2/0 G AWG;2/0 J AWG;2/0 K AWG;2/0 V AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE/FLEX
Wire Size	2/0 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Dimension - Z (inch) 0.36 in
Physical Attribute - Tongue Angle Straight

Electrical Ratings

Voltage - Maximum 35000
Voltage Rating 35 kV

Logistics

Carton Quantity 100
Minimum Pack Quantity 1
Pallet Quantity 29000

Product Assets

[3D Models - YAV26LTC516FX_MODEL-IGES](#)
[3D Models - YAV26LTC516FX_MODEL-PDF](#)
[3D Models - YAV26LTC516FX_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SE..208001-01](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAV26LTC516FX-SPEC-EN | REV 5/2024