



## YAV272NFXB, Cu Compression, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Long Barrel, 3/0 Flex

By Burndy  
Catalog # YAV272NFXB



3/0 Flex G,H,I,K,M,DLO, 3/0 AWG CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel, Bell End, Tin Plated, UL/CSA, 90°C, Up to 35kV, Orange Color Code, 14 Die Index.

### Application

Wire Termination

### General

Catalog Number	YAV272NFXB
Color Code	Orange
Connector Type	LONG BARREL
Die Index	14
EU RoHS Indicator	Yes
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810076675
UPC 12 Digit	7818100766755

### Dimensions

Dimension - B Length inch	1.64 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	132 mm
Dimension - Length Overall inch	5.20 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Pad Width inch	1.03 in
Dimension - Strip Length inch	1-13/16
Dimension - Stud Size fraction	1/2
Dimension - Stud Size inch	1/2
Dimension - Z (inch)	0.64 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper DLO Size	3/0 AWG
Conductor - Copper DLO Size Range	3/0 AWG
Conductor - Copper Flex G Size	"3/0 AWG"
Conductor - Copper Flex G Size Range	3/0 AWG
Conductor - Copper Flex H Size	"3/0 AWG"
Conductor - Copper Flex H Size Range	3/0 AWG
Conductor - Copper Flex I Size	"3/0 AWG"
Conductor - Copper Flex I Size Range	3/0 AWG
Conductor - Copper Flex K Size	"3/0 AWG"
Conductor - Copper Flex K Size Range	3/0 AWG
Conductor - Copper Flex M Size	"3/0 AWG"
Conductor - Copper Str Compact Size	"3/0 AWG"
Conductor - Copper Str Navy Size	150
Conductor - Copper Str Size	"3/0 AWG"
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Material	COPPER
Conductor Size	3/0 AWG
Conductor Type	CODE/FLEX
Wire Size	3/0 AWG

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	8700

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Copper Flex Long Terminals Tooling and Installation Instructions](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SE..208074-01](#)  
[Specifications - YAV272NFXB](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand