

Compression Terminal

By Burndy
Catalog # [YAV27LTC10FX90](#)

3/0 Flex G,H,I,K,M,DLO, 3/0 AWG CU, One Hole, #10 Stud Size, Standard Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Orange Color Code, 14 Die Index.



Application

Wire Termination

General

Color Code	Orange
Connector Type	STANDARD BARREL
Die Index	14
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810322826
UPC 12 Digit	7818103228266

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.00 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - Bolt Size fraction	#8-#10
Dimension - Bolt Size inch	0.21
Dimension - Hole Size fraction	#10
Dimension - Hole Size inch	0.21
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	0.98 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Pad Width inch	1.03 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size fraction	#10
Dimension - Z inch	0.27 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Conductor Related

Conductor - Copper DLO Size	3/0 AWG
Conductor - Copper DLO Size Range	3/0 AWG
Conductor - Copper Flex G Size	"3/0 AWG"
Conductor - Copper Flex G Size Range	3/0 AWG
Conductor - Copper Flex H Size	"3/0 AWG"
Conductor - Copper Flex H Size Range	3/0 AWG
Conductor - Copper Flex I Size	"3/0 AWG"
Conductor - Copper Flex I Size Range	3/0 AWG
Conductor - Copper Flex K Size	"3/0 AWG"
Conductor - Copper Flex K Size Range	3/0 AWG
Conductor - Copper Flex M Size	"3/0 AWG"
Conductor - Copper Str Compact Size	"3/0 AWG"
Conductor - Copper Str Navy Size	150
Conductor - Copper Str Size	"3/0 AWG"
Conductor - Copper Str Size Range	3/0 AWG
Conductor - CopperWeld Str Size	3/0 E AWG;3/0 EK AWG;3/0 F AWG;3/0 G AWG;3/0 J AWG;3/0 V AWG
Conductor - Material	COPPER
Conductor Size	3/0 AWG
Conductor Type	CODE/FLEX
Wire Size	3/0 AWG

Certifications and Compliance

Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Sales Drawings - SE..208001-02](#)

Voltage - Maximum
Voltage Rating

35000
35 kV

[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAV27LTC10FX90-SPEC-EN | REV 8/2023