

# Uninsulated Ring Terminal For 4/0 AWG

By Burndy  
Catalog # [YAV28L13BR](#)



Uninsulated Ring Terminal For 4/0 AWG.

## General

Connector Type	Ring Terminal
Die Index	46
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Bright
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810136355

## Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.85 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size mm	17 mm
Dimension - Length Overall inch	2.72 in
Dimension - N inch	0.56 in
Dimension - Pad Width inch	1.12 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size inch	5/8 in
Dimension - Z inch	0.60 in
Physical Attribute - Tongue Angle	Straight

## Conductor Related

Conductor - Copper Str Aircraft Size	AN-4/0
Conductor Size	4/0 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	100
-----------------------	-----

## Product Assets

[Sales Drawings - 50094161\\_E](#)