

Compression Terminal

By Burndy
Catalog # [YAV28L2ENT14FX](#)

4/0 Flex G,H,I,K,M,DLO, 4/0 AWG CU, Two Hole, 1/4 Stud Size, 5/8 Hole Spacing, Standard Barrel, Inspection Window, Narrow Tongue, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Purple Color Code, 15 Die Index.



Application

Wire Termination

General

Color Code	Purple
Connector Type	STANDARD BARREL
Die Index	15
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YAV-L-NTFX
UPC	781810250730

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.03 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Diameter Min Size inch	1.28 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	73 mm
Dimension - Length Overall inch	2.86 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.77 in
Dimension - Pad Width inch	0.76 in
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4

Conductor Related

Conductor - Copper DLO Size	4/0 AWG
Conductor - Copper DLO Size Range	4/0 AWG
Conductor - Copper Flex G Size	"4/0 AWG"
Conductor - Copper Flex G Size Range	4/0 AWG
Conductor - Copper Flex H Size	"4/0 AWG"
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	"4/0 AWG"
Conductor - Copper Flex I Size Range	4/0 AWG
Conductor - Copper Flex K Size	"4/0 AWG"
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex M Size	"4/0 AWG"
Conductor - Copper Str Compact Size	"4/0 AWG"
Conductor - Copper Str Navy Size	200
Conductor - Copper Str Size	"4/0 AWG"
Conductor - Copper Str Size Range	4/0 AWG
Conductor - CopperWeld Str Size	4/0 E AWG;4/0 EK AWG;4/0 F AWG;4/0 G AWG;4/0 V AWG
Conductor - Material	COPPER
Conductor Size	4/0 AWG
Conductor Type	CODE/FLEX
Wire Size	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Dimension - Z inch 0.34 in
Physical Attribute - Tongue Angle Straight

Electrical Ratings

Voltage - Maximum 35000
Voltage Rating 35 kV

Logistics

Carton Quantity 50
Minimum Pack Quantity 50
Pallet Quantity 14800

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
[Sales Drawings - 30003952](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAV28L2ENT14FX-SPEC-EN | REV 8/2023