

# Uninsulated Ring Terminal For 4/0 AWG

By Burndy  
Catalog # [YAV28L53](#)



Uninsulated Ring Terminal For 4/0 AWG.

## Application

For Copper Aircraft Cable

## General

Connector Type	Ring Terminal
Die Index	46
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none"><li>DLP Copper</li><li>Tin Plating</li></ul>
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810224861

## Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.85 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size mm	7 mm
Dimension - Length Overall inch	2.28 in
Dimension - N inch	0.44 in
Dimension - Pad Width inch	1.12 in
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.28 in
Physical Attribute - Tongue Angle	Straight

## Conductor Related

Conductor - Copper Str Aircraft Size	AN-4/0
Conductor Size	4/0 AWG
Conductor Type	<ul style="list-style-type: none"><li>CU C Solid-Size</li><li>CU C Str-Size</li></ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	14800

## Product Assets

[Sales Drawings - 50094161\\_E](#)

