

Uninsulated Ring Terminal For 4/0 AWG

By Burndy
Catalog # [YAV28L56](#)



Copper Compression Lug, 1 Hole W/ Inspection Window, AN 4/0 Flex, 5/16" Stud, Short Barrel, Tin Plated

Application

For Copper AirCRAFT Cable

General

Connector Type	Ring Terminal
Construction Material - Main	Copper tubing
Die Index	46
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none"> • DLP Copper • Tin Plating
Military Specification	MS20659
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	Terminals, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810093801

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.85 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Hole Size mm	8 mm
Dimension - Length Overall inch	2.72 in
Dimension - N inch	0.56 in
Dimension - Pad Width inch	1.12 in
Dimension - Stud Size inch	5/16 in
Dimension - Z inch	0.60 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Aircraft Size	AN-4/0
Conductor Size	4/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • Military Specified (Mil-Spec)
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	14800

Product Assets

[3D Models - YAV28L56_MODEL-STEP](#)
[3D Models - YAV28L56_MODEL-IGES](#)
[3D Models - YAV28L56_MODEL-PDF](#)
[Sales Drawings - 50094161_E](#)

