



Uninsulated Ring Terminal For 4/0 AWG

By Burndy
Catalog # [YAV28LG78](#)



Uninsulated Ring Terminal For 4/0 AWG.

General

Connector Type	Ring Terminal
Die Index	46
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none">DLP CopperTin Plating

Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810368855

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size mm	10 mm
Dimension - Length Overall inch	2.56 in
Dimension - N inch	0.38 in
Dimension - Outside Diameter inch	0.77 in
Dimension - Pad Width inch	0.63 in
Dimension - Stud Size inch	3/8 in
Dimension - Z (inch)	0.60 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Aircraft Size	AN 4/0
Conductor Size	4/0 AWG
Conductor Type	<ul style="list-style-type: none">CU C Solid-SizeCU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	24000

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 10100269](#)



A proud member of the Hubbell Family.