

Compression Terminal

By Burndy
Catalog # [YAV29LTC34FX](#)

250 kcmil, 4/0 G,H,I,K,M,DLO CU, One Hole, 3/4 Stud Size, Standard Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Yellow Color Code, 16 Die Index.



Application

Wire Termination

General

Color Code	Yellow
Connector Type	STANDARD BARREL
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810311400
UPC 12 Digit	7818103114000

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.03 in
Dimension - Bolt Hole Size inch	0.91 in
Dimension - Bolt Size fraction	3/4
Dimension - Bolt Size inch	0.75
Dimension - Hole Size fraction	3/4
Dimension - Hole Size inch	0.81
Dimension - Hole Size mm	21 mm
Dimension - L Length Overall mm	79 mm
Dimension - Length Overall inch	3.11 in
Dimension - N inch	0.75 in
Dimension - Outside Diameter inch	0.80 in
Dimension - Pad Width inch	1.18 in
Dimension - Strip Length inch	1-1/16
Dimension - Stud Size fraction	3/4
Dimension - Stud Size inch	3/4
Dimension - Thread Size	3/4 in
Dimension - Z inch	0.77 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper DLO Size	4/0 AWG
Conductor - Copper DLO Size Range	4/0 AWG
Conductor - Copper Flex G Size	"4/0 AWG"
Conductor - Copper Flex G Size Range	4/0 AWG
Conductor - Copper Flex H Size	"4/0 AWG"
Conductor - Copper Flex H Size Range	4/0 AWG
Conductor - Copper Flex I Size	"4/0 AWG"
Conductor - Copper Flex I Size Range	4/0 AWG
Conductor - Copper Flex K Size	"4/0 AWG"
Conductor - Copper Flex K Size Range	4/0 AWG
Conductor - Copper Flex M Size	"4/0 AWG"
Conductor - Copper Str Compact Size	"4/0 AWG"
Conductor - Copper Str Navy Size	200
Conductor - Copper Str Size	"4/0 AWG"
Conductor - Copper Str Size Range	250 kcmil
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	CODE/FLEX
Wire Size	250 KCMIL

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	20
Minimum Pack Quantity	20

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Minimum Pack Quantity	20
Pallet Quantity	11520

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
[Sales Drawings - SE214481-01_C](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAV29LTC34FX-SPEC-EN | REV 8/2023