



YAV2CLNT14FX, Cu Compression, 1-Hole, 1/4" Stud, Standard Barrel, Narrow Tongue, 2 Flex

By Burndy
Catalog # [YAV2CLNT14FX](#)



2 Flex G,H,I,K,M,DLO, 2 AWG CU, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window, Narrow Tongue Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Brown Color Code, 10 Die Index.

Application

Wire Termination

General

Color Code	Brown
Connector Type	STANDARD BARREL
Die Index	10
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YAV-L-NTFX
UPC	781810326138

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.63 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.71 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.46 in
Dimension - Strip Length inch	11/16
Dimension - Stud Size fraction	1/4
Dimension - Stud Size inch	1/4
Dimension - Z (inch)	0.33 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper DLO Size	2 AWG
Conductor - Copper DLO Size Range	2 AWG
Conductor - Copper Flex G Size	"2 AWG"
Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Flex H Size	"2 AWG"
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	"2 AWG"
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex K Size	"2 AWG"
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex M Size	"2 AWG"
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Compact Size	"2 AWG"
Conductor - Copper Str Navy Size	60
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Size	"2 AWG"
Conductor - Copper Str Size Range	2 AWG
Conductor - CopperWeld Str Size	2 A AWG;2 F AWG;2 G AWG;2 J AWG;2 K AWG;2 N AWG;2 P AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE/FLEX
Wire Size	2 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Status

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	50
Minimum Pack Quantity	50
Pallet Quantity	48000

Product Assets

- [3D Models - YAV2CLNT14FX_MODEL-PDF](#)
- [3D Models - YAV2CLNT14FX_MODEL-STEP](#)
- [3D Models - YAV2CLNT14FX_MODEL-IGES](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)
- [Product Cross Section Image\(s\) - BUR_YAL2NTRFX_Lineart](#)
- [Sales Drawings - 30003952](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAV2CLNT14FX-SPEC-EN | REV 5/2024