

Uninsulated Right Angle Ring Terminal For 2 AWG (Nickel Plated)

By Burndy
Catalog # [YAV2CRS2NK](#)



Uninsulated Right Angle Ring Terminal For 2 AWG (Nickel Plated).

General

Connector Type	Ring Terminal
Die Index	41
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810069738

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.62 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - G inch	1 in
Dimension - Hole Size mm	8 mm
Dimension - Length Overall inch	1.27 in
Dimension - N inch	0.33 in
Dimension - Outside Diameter inch	0.47 in
Dimension - Pad Width inch	0.68 in
Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	5/16 in
Dimension - Z (inch)	0.34 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN 2
Conductor Size	2 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	200
Minimum Pack Quantity	200
Pallet Quantity	46400

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 50094166](#)