

# Compression Terminal

By Burndy  
Catalog # [YAV352M10](#)

Non insulated Cu tubular terminals, Metric, 2 Holes/W/insp W, 35mmClass2,5, 3/8" stud, Tin - Electro Plated, 10 Index.



## Application

Metric Wire Termination

## General

Connector Type	METRIC
Die Index	10
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810636503
UPC 12 Digit	7818106365033

## Dimensions

Bolt Size	M10
Dimension - B Length inch	16.0 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	91 mm
Dimension - Length Overall inch	3.57 in
Dimension - N inch	0.41 in
Dimension - Pad Width inch	17.3 in
Dimension - Strip Length inch	0.67 in
Dimension - Stud Size fraction	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight
Thickness - Pad	0.10 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	35 mm <sup>2</sup> , 2 AWG
Conductor - Material	COPPER
Conductor Size	35 mm <sup>2</sup>
Conductor Type	CLASS 2

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	50
Minimum Pack Quantity	50

## Product Assets

[3D Models - YAV352M10\\_MODEL-IGES](#)  
[3D Models - YAV352M10\\_MODEL-PDF](#)  
[3D Models - YAV352M10\\_MODEL-STEP](#)  
[Sales Drawings - 50025887](#)