

## YAV352M8, Compression Terminal

By Burndy

Catalog # [YAV352M8](#)

HYLUG™ Copper tubing Compression terminals, 35 mm, M8 Stud, 2 Holes, Tin Plated.



### Application

Metric Wire Termination

### General

Catalog Number	YAV352M8
Connector Type	METRIC
Die Index	10
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637838
UPC 12 Digit	7818106378388

### Dimensions

Dimension - B Length inch	16.0 in
Dimension - Bolt Size fraction	5/16
Dimension - Bolt Size inch	0.3125
Dimension - Hole Size fraction	5/16
Dimension - Hole Size inch	0.38
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	91 mm
Dimension - Length Overall inch	3.57 in
Dimension - Pad Width inch	17.3 in
Dimension - Strip Length inch	0.67 in
Dimension - Stud Size fraction	5/16
Dimension - Z (inch)	0.36 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Material	COPPER
Conductor Size	35 mm <sup>2</sup>
Conductor Type	CLASS 2

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	50
Minimum Pack Quantity	50
Pallet Quantity	28800

### Product Assets

- [3D Models - YAV352M8\\_MODEL-PDF](#)
- [3D Models - YAV352M8\\_MODEL-IGES](#)
- [3D Models - YAV352M8\\_MODEL-STEP](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_yavm\\_lineart](#)
- [Sales Drawings - 50025887](#)
- [Specifications - YAV352M8](#)