

Compression Terminal

By Burndy
Catalog # [YAV4002M20](#)

HYLUG™ Copper tubing Compression terminals, 400 mm, M20 Stud, 2 Holes, Tin Plated.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	24
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810637999
UPC 12 Digit	7818106379999

Dimensions

Dimension - B Length inch	7.6 in
Dimension - Bolt Size fraction	7/8
Dimension - Bolt Size inch	0.88
Dimension - Hole Size fraction	7/8
Dimension - Hole Size inch	0.94
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	149 mm
Dimension - Length Overall inch	5.88 in
Dimension - Pad Width inch	50.3 in
Dimension - Strip Length inch	1.46 in
Dimension - Stud Size fraction	7/8
Dimension - Z (inch)	0.89 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Material	COPPER
Conductor Size	400 mm ²
Conductor Type	CLASS 2

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	5
-----------------------	---

Product Assets

[3D Models - YAV4002M20_MODEL-STEP](#)
[3D Models - YAV4002M20_MODEL-IGES](#)
[3D Models - YAV4002M20_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
[Sales Drawings - 50025887](#)