



Compression Terminal

By Burndy
Catalog # [YAV400FM14](#)

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 400 mm, 14 mm Stud, 3.47 IN L, Compression, 24 Index, 37 mm Strip Length.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	24
Feature - Barrel Style	<ul style="list-style-type: none">• Chamfered• Skived
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810323496
UPC 12 Digit	7818103234966

Dimensions

Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.42 in
Dimension - Bolt Hole Size inch	0.25 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - Inside Diameter inch	1.07 in
Dimension - L Length Overall mm	99 mm
Dimension - Length Overall inch	3.90 in
Dimension - N inch	0.61 in
Dimension - Outside Diameter inch	1.38 in
Dimension - Pad Width inch	1.98 in
Dimension - Strip Length inch	1.46 in
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.57 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Material	COPPER
Conductor Size	400 mm ²
Conductor Type	CLASS 5

Certifications And Compliance

Standards - RoHS Compliance Status CM

Logistics

Minimum Pack Quantity 5

Product Assets

[3D Models - YAV400FM14_MODEL-STEP](#)
[3D Models - YAV400FM14_MODEL-IGES](#)
[3D Models - YAV400FM14_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
[Sales Drawings - 50025612](#)



A proud member of the Hubbell Family.