



YAV4CL2NT10FX90, Compression Terminal, 4 Flex G,H,I,K,M, DLO, 4 AWG, Cu, 2-Hole, #10 Stud, 5/8" Spacing, Standard Barrel, Narrow Tongue, 90 Degree

By Burndy

Catalog # [YAV4CL2NT10FX90](#)

Cu Comp Terminal Flex Cond, 2 Hole/W/InspWindow, #4 Weld, 5(91/#24)-4(105/#24)DLO Flex, #4 AWG Code, 40&50 Navy, 600 V-35 kV, #10 Stud, 90 Deg Bent, Std bbl.



Application

Wire Termination

General

Catalog Number	YAV4CL2NT10FX90
Color Code	Gray
Connector Type	STANDARD BARREL
Die Index	8
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810323571
UPC 12 Digit	7818103235711

Dimensions

Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.21 in
Dimension - Bolt Size fraction	#8-#10
Dimension - Bolt Size inch	0.21
Dimension - D inch	1.15 in
Dimension - Height inch	0.91 in
Dimension - Hole Size fraction	#10
Dimension - Hole Size inch	0.21
Dimension - Hole Size mm	5.3 mm
Dimension - L Length Overall mm	35 mm
Dimension - Length Overall inch	1.39 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Pad Width inch	0.45 in
Dimension - Strip Length inch	9/16
Dimension - Stud Size fraction	#10
Dimension - Z (inch)	0.26 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	4 AWG
Conductor - Copper DLO Size	4 AWG
Range	
Conductor - Copper Flex G Size	"4 AWG"
Conductor - Copper Flex G Size	4 AWG
Range	
Conductor - Copper Flex H Size	"4 AWG"
Conductor - Copper Flex H Size	4 AWG
Range	
Conductor - Copper Flex I Size	"4 AWG"
Conductor - Copper Flex I Size	4 AWG
Range	
Conductor - Copper Flex K Size	"4 AWG"
Conductor - Copper Flex K Size	4 AWG
Range	
Conductor - Copper Flex M	"4 AWG"
Size	
Conductor - Copper Flex M	4 AWG
Size Range	
Conductor - Copper Solid Size	4 AWG
Conductor - Copper Str	"4 AWG"
Compact Size	
Conductor - Copper Str Navy	40
Size	
Conductor - Copper Str Navy	40 (19) Navy-50 (19) Navy
Size Range	
Conductor - Copper Str Size	"4 AWG"
Conductor - Copper Str Size	4 AWG
Range	
Conductor - CopperWeld Str	4 A AWG;4 D AWG;4 N AWG;4
Size	P AWG
Conductor - CopperWeld Str	4 A AWG-4 P AWG
Size Range	
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE/FLEX
Wire Size	4 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	50
Minimum Pack Quantity	50

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..208119-01](#)
[Specifications - YAV4CL2NT10FX90](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAV4CL2NT10FX90-SPEC-EN | REV 8/2024