

Uninsulated Ring Terminal For 4 AWG

By Burndy
Catalog # [YAV4CL45](#)



Uninsulated Ring Terminal For 4 AWG.

General

Connector Type	Ring Terminal
Die Index	40
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none"> • DLP Copper • Tin Plating
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810287750
UPC 12 Digit	7818102877500

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - D inch	0.53 in
Dimension - Length Overall inch	1.15 in
Dimension - N inch	0.25 in
Dimension - Pad Width inch	0.55 in
Dimension - Z inch	0.28 in
Physical Attribute - Tongue Angle	45 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN 4
Conductor - Copper Str Aircraft Size Range	AN 4
Conductor Size	4 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	2000
-----------------------	------

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50103883](#)
[Technical Solutions - BURNDY_YAV4CL45_Specsheet](#)