

# Compression Terminal

By Burndy  
Catalog # [YAV4CLTC14FX](#)

4 Flex G,H,I,K,M,DLO, 4 AWG CU, One Hole, 1/4 Stud Size, Standard Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Gray Color Code, 8 or 346 Die Index.



## Application

Wire Termination

## General

Color Code	Gray
Connector Type	STANDARD BARREL
Die Index	8
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810022573
UPC 12 Digit	7818100225733

## Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - D inch	0.64 in
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	37 mm
Dimension - Length Overall inch	1.44 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.38 in
Dimension - Pad Width inch	0.55 in
Dimension - Strip Length inch	1/2
Dimension - Strip Length mm	12.7

## Conductor Related

Conductor - Copper DLO Size	4 AWG
Conductor - Copper DLO Size Range	4 AWG
Conductor - Copper Flex G Size	"4 AWG"
Conductor - Copper Flex G Size Range	4 AWG
Conductor - Copper Flex H Size	"4 AWG"
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Size	"4 AWG"
Conductor - Copper Flex I Size Range	4 AWG
Conductor - Copper Flex K Size	"4 AWG"
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex M Size	"4 AWG"
Conductor - Copper Flex M Size Range	4 AWG
Conductor - Copper Solid Size	4 AWG
Conductor - Copper Solid Size Range	4 AWG
Conductor - Copper Str Compact Size	"4 AWG"
Conductor - Copper Str Navy Size	40
Conductor - Copper Str Navy Size Range	40 (19) Navy-50 (19) Navy
Conductor - Copper Str Size	"4 AWG"
Conductor - Copper Str Size Range	4 AWG
Conductor - CopperWeld Str Size	4 A AWG;4 D AWG;4 N AWG;4 P AWG
Conductor - CopperWeld Str Size Range	4 A AWG-4 P AWG
Conductor - Material	COPPER
Conductor Size	4 AWG
Conductor Type	CODE/FLEX
Wire Size	4 AWG

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - UL Approved	Yes

Dimension - Stud Size fraction 1/4  
Dimension - Stud Size inch 1/4  
Dimension - Z inch 0.33 in  
Physical Attribute - Tongue Angle Straight

### Electrical Ratings

Voltage - Maximum 35000  
Voltage Rating 35 kV

Certification - UL Recognized No  
Industry Standard(s) UL 486A-486B

### Logistics

Carton Quantity 50  
Minimum Pack Quantity 1

### Product Assets

[3D Models - YAV4CLTC14FX\\_MODEL-PDF](#)  
[3D Models - YAV4CLTC14FX\\_MODEL-STEP](#)  
[3D Models - YAV4CLTC14FX\\_MODEL-IGES](#)  
[Customer Notices - Prop 65 Notice](#)  
[Installation Manuals - Copper Flex Standard Terminals Tooling and Installation Instructions](#)  
[Sales Drawings - SE..208001-01](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YAV4CLTC14FX-SPEC-EN | REV 6/2023