

Compression Terminal

By Burndy
Catalog # [YAV500M20](#)

Copper Tubing Terminal, 1 Hole W/insp window, 500 mm Class 2, L115 Index, 20 mm Stud.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	L115
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810323687
UPC 12 Digit	7818103236877

Dimensions

Dimension - B Length fraction	2-3/16 in
Dimension - B Length inch	0.65 in
Dimension - Bolt Size fraction	7/8
Dimension - Bolt Size inch	0.88
Dimension - D inch	1.81 in
Dimension - Hole Size fraction	7/8
Dimension - Hole Size inch	0.94
Dimension - Hole Size mm	23.8 mm
Dimension - Inside Diameter inch	1.17 in
Dimension - L Length Overall mm	8 mm
Dimension - Length Overall inch	0.33 in
Dimension - N inch	0.88 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	0.19 in
Dimension - Strip Length inch	1.69 in
Dimension - Stud Size fraction	7/8
Dimension - Z (inch)	0.89 in
Physical Attribute - Tongue	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Material	COPPER
Conductor Size	500 mm ²
Conductor Type	CLASS 2

Certifications And Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	100
-----------------------	-----

Product Assets

[3D Models - YAV500M20_MODEL-IGES](#)
[3D Models - YAV500M20_MODEL-STEP](#)
[3D Models - YAV500M20_MODEL-PDF](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_yavm_lineart](#)
[Sales Drawings - 50025521](#)



A proud member of the Hubbell Family.