



## YAV50F2M14, Compression Terminal

By Burndy  
Catalog # [YAV50F2M14](#)

Cu Compression Lug, 2 Hole, W/Inspection Window, 50 mm, M14 Stud, 44.5 mm Spacing, Standard Barrel, 19 mm Wire Strip Length.



### Application

Metric Wire Termination

### General

Catalog Number	YAV50F2M14
Connector Type	METRIC
Die Index	12
Finish Type	Tin-Plated
Material	COPPER
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810640678
UPC 12 Digit	7818106406788

### Dimensions

Dimension - B Length inch	0.69 in
Dimension - Bolt Hole Size inch	0.59 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	101.3 mm
Dimension - Length Overall inch	3.99 in
Dimension - N inch	0.55 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.88 in
Dimension - Strip Length inch	0.69 in
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.57 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Material	COPPER
Conductor Size	50 mm <sup>2</sup>
Conductor Type	CLASS 2

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	20
-----------------------	----

### Product Assets

- [3D Models - YAV50F2M14\\_MODEL-PDF](#)
- [3D Models - YAV50F2M14\\_MODEL-STEP](#)
- [3D Models - YAV50F2M14\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_yavm\\_lineart](#)
- [Sales Drawings - 50025888](#)
- [Specifications - YAV50F2M14](#)



A Hubbell brand