

Compression Terminal

By Burndy
Catalog # [YAV50FM12](#)

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 50 mm, M12 Stud, 2.19 IN L, Compression, 12 Index, 19 mm Strip Length.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	12
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810243121
UPC 12 Digit	7818102431211

Dimensions

Dimension - B Length inch	0.69 in
Dimension - Bolt Hole Size inch	0.53 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	55.6mm
Dimension - Length Overall inch	2.19 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	0.69 in
Dimension - Stud Size fraction	1/2
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Material	COPPER
Conductor Size	50 mm ²
Conductor Type	CLASS 5

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	20

Product Assets

[3D Models - YAV50FM12_MODEL-IGES](#)
[3D Models - YAV50FM12_MODEL-PDF](#)
[3D Models - YAV50FM12_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025612](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAV50FM12-SPEC-EN | REV 8/2023