



Compression Terminal

By Burndy
Catalog # [YAV6302M16](#)

HYLUG™ Copper tubing Compression terminals, 630 mm, M16 Stud, 2 Holes, Tin Plated.



Application

Metric Wire Termination

General

Connector Type	METRIC
Die Index	29
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638026
UPC 12 Digit	7818106380266

Dimensions

Dimension - B Length inch	9.7 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.63
Dimension - Hole Size fraction	5/8
Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	159 mm
Dimension - Length Overall inch	6.25 in
Dimension - Pad Width inch	62.5 in
Dimension - Strip Length inch	2.17 in
Dimension - Stud Size fraction	5/8
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Material	COPPER
Conductor Size	630 mm ²
Conductor Type	CLASS 2

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	2
Minimum Pack Quantity	2

Product Assets

[3D Models - YAV6302M16_MODEL-IGES](#)
[3D Models - YAV6302M16_MODEL-PDF](#)
[3D Models - YAV6302M16_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 50025887](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAV6302M16-SPEC-EN | REV 8/2023