



# Compression Terminal

By Burndy  
Catalog # [YAV6302M20](#)

HYLUG™ Copper tubing Compression terminals, 630 mm, M20 Stud, 2 Holes, Tin Plated.



## Application

Metric Wire Termination

## General

Connector Type	METRIC
Die Index	29
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638033
UPC 12 Digit	7818106380333

## Dimensions

Dimension - B Length inch	9.7 in
Dimension - Bolt Size fraction	7/8
Dimension - Bolt Size inch	0.88
Dimension - Hole Size fraction	7/8
Dimension - Hole Size inch	0.94
Dimension - Hole Size mm	23.8 mm
Dimension - L Length Overall mm	170 mm
Dimension - Length Overall inch	6.69 in
Dimension - Pad Width inch	62.5 in
Dimension - Strip Length inch	2.17 in
Dimension - Stud Size fraction	7/8
Dimension - Z inch	0.89 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Material	COPPER
Conductor Size	630 mm <sup>2</sup>
Conductor Type	CLASS 2

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	2
Minimum Pack Quantity	2

## Product Assets

[3D Models - YAV6302M20\\_MODEL-PDF](#)  
[3D Models - YAV6302M20\\_MODEL-STEP](#)  
[3D Models - YAV6302M20\\_MODEL-IGES](#)  
[Catalogs - Full Line BURNDY Catalog](#)  
[Sales Drawings - 50025887](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YAV6302M20-SPEC-EN | REV 8/2023