



YAV6CL2TC14FX45, Compression Terminal, 6 Flex G,H,I,K,M, DLO, 6 AWG, Cu, 2-Hole, 1/4" Stud, 5/8" Spacing, Standard Barrel, 45 Degree



By Burndy
Catalog # [YAV6CL2TC14FX45](#)

Cu Comp Terminal Flex Cond, 2 Hole/W/InspWindow, #6 Weld, 6(61/#24)DLO Flex, #6 AWG Code, 30 Navy, 600 V-35 kV, 1/4" Stud, 0.63" Spacing, 45 Deg Bent, Std bbl.

Application

Wire Termination

General

Catalog Number	YAV6CL2TC14FX45
Color Code	Blue
Connector Type	STANDARD BARREL
Die Index	7
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none">• Chamfered• Skived
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810022894
UPC 12 Digit	7818100228944

Dimensions

Dimension - B Length fraction	1/2 in
Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Bolt Size inch	0.25
Dimension - Hole Size fraction	1/4
Dimension - Hole Size inch	0.27
Dimension - Hole Size mm	6.9 mm
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.02 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Pad Width inch	0.48 in
Dimension - Strip Length inch	9/16 in
Dimension - Stud Size fraction	1/4
Dimension - Z (inch)	0.34 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	6 AWG
Conductor - Copper DLO Size	6 AWG
Range	
Conductor - Copper Flex G Size	"6 AWG"
Conductor - Copper Flex G Size	6 AWG
Range	
Conductor - Copper Flex H Size	"6 AWG"
Conductor - Copper Flex H Size	6 AWG
Range	
Conductor - Copper Flex I Size	"6 AWG"
Conductor - Copper Flex I Size	6 AWG
Range	
Conductor - Copper Flex K Size	"6 AWG"
Conductor - Copper Flex K Size	6 AWG
Range	
Conductor - Copper Flex M	"6 AWG"
Size	
Conductor - Copper Flex M	6 AWG
Size Range	
Conductor - Copper Solid Size	6 AWG
Conductor - Copper Solid Size	6 Sol
Range	
Conductor - Copper Str	"6 AWG"
Compact Size	
Conductor - Copper Str Navy	30
Size	
Conductor - Copper Str Navy	30 Navy
Size Range	
Conductor - Copper Str Size	"6 AWG"
Conductor - Copper Str Size	6 AWG
Range	
Conductor - CopperWeld Str	#6 WELD (61/24)
Size	
Conductor - CopperWeld Str	#6 WELD (61/24)
Size Range	
Conductor - Material	COPPER
Conductor Size	6 AWG
Conductor Type	CODE/FLEX
Wire Size	6 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - SE..208119-01](#)
[Specifications - YAV6CL2TC14FX45](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAV6CL2TC14FX45-SPEC-EN | REV 8/2024