

# **Compression Terminal**

By Burndy Catalog # YAV70M10

Non insulated Cu tubular terminals, Metric, 1 Hole/W/insp W, 70mmClass2, 3/8" stud, Tin - Electro Plated.



#### **Application**

Metric Wire Termination

## General

Connector Type **MFTRIC** Construction Material - Main Copper tubing Die Index 1.3 EU RoHS Indicator Yes Chamfered Feature - Barrel Style Skived Finish Type Tin-Plated Material **COPPER** 

Physical Attribute - Number of 1

Holes

Physical Attribute - Tongue Ring

Type

Plated

Plating Type Tin - Electro Plated Sub Brand Terminals, HYLUG

Trade Name HYLUG™ Туре YAV

UPC 781810328200

## **Dimensions**

Dimension - B Length fraction 13/16 in Dimension - B Length inch 0.69 in Dimension - Bolt Size fraction 3/8 Dimension - Bolt Size inch 0.38 Dimension - Hole Size fraction 3/8 Dimension - Hole Size inch 10.4 mm Dimension - Hole Size mm Dimension - Length Overall 1.94 in inch Dimension - N inch 0.39 in Dimension - Outside Diameter 0.56 in inch Dimension - Pad Width inch 0.83 in Dimension - Strip Length inch 0.75 in Dimension - Stud Size fraction 3/8 Dimension - Z inch 0.42 in Physical Attribute - Tongue Straight Angle

## **Electrical Ratings**

Voltage - Maximum 35000 Voltage Rating 35 kV

#### **Conductor Related**

Conductor - Copper Str Size 1/0 Conductor - Material COPPER Conductor Size 70 mm2 CLASS 2 Conductor Type

#### **Certifications and Compliance**

Certification - CSA Approved Nο Certification - ETL No Certification - UL Recognized Nο Certification - cULus Standards - RoHS Compliance Status **UL** Listed Nο

## Logistics

Carton Quantity 20 Minimum Pack Quantity 20

#### **Product Assets**

3D Models - YAV70M10\_MODEL-STEP 3D Models - YAV70M10 MODEL-PDF 3D Models - YAV70M10 MODEL-IGES

Sales Drawings - 50025521

