



## YAV8CL3, Uninsulated Ring Terminal For 8 AWG

By Burndy  
Catalog # [YAV8CL3](#)

Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole w/ Inspection Window, AN 8 Flex, 3/8" Stud, Short Barrel, Tin Plated.

### Features

- Manufactured from seamless pure electrolytic copper tubing to provide maximum conductivity, low resistance and excellent ductility for crimping
- Seamless tubular crimp barrel design - No seams to split resulting in a very high quality electrical connection, also can be used on solid conductor
- Double thick tongue structurally a very strong terminal tongue
- Produced from tubular copper, extra copper material assures the compression connector will operate cooler than the conductors it connects
- Internally bevelled barrel for easy cable entry, especially for flexible conductors
- Inspection hole provides easy visual check for proper conductor insertion
- Electro-tin plated for a long lasting durable corrosion resistance

### Application

Industrials, Hospitals, Utilities, Marine, Computer

### General

Application - For Use On	Copper Commercial (Code) Cable, Type AN Aircraft Cable, Extra Flexible Conductor
Catalog Number	YAV8CL3
Connector Type	Ring Terminal
Die Index	38
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none"><li>• DLP Copper</li><li>• Tin Plating</li></ul>
Military Specification	AS20659
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated



Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810025123
UPC 14 Digit GTIN	00781810025123

### Dimensions

Dimension - B Length fraction	2/5 in
Dimension - B Length inch	0.41 in
Dimension - Bolt Size fraction	3/8
Dimension - Length Overall inch	1.29 in
Dimension - N inch	0.28 in
Dimension - Pad Width inch	0.57 in
Dimension - Stud Size inch	3/8
Dimension - Z (inch)	0.34 in

### Conductor Related

Conductor - Copper Str Aircraft Size	AN 8
Conductor - Copper Str Size	8
Conductor - Copper Str Size Range	8 AWG
Conductor Size	8 AWG
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"><li>• UL467</li><li>• Military Specified (Mil-Spec)</li></ul>
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	200
Minimum Pack Quantity	200
Pallet Quantity	99999

Product Assets

- Catalogs - BURNDY Master Catalog - Section B - Small Terminals
- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Product Cross Section Image(s) - BUR\_YAV10L36BOX\_LineArt
- Sales Drawings - 50094161\_E
- Specifications - YAV8CL3

