

# Compression Terminal

By Burndy  
Catalog # [YAV952M16](#)

Hylug Copper tubing Compression terminals,95 mm<sup>2</sup>,M16 Stud, 2 Holes,Tin Plated.



## Application

Metric Wire Termination

## General

Connector Type	METRIC
Die Index	14
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810638187

## Dimensions

Dimension - B Length inch	20.6 in
Dimension - Bolt Size fraction	5/8
Dimension - Bolt Size inch	0.63
Dimension - Hole Size fraction	5/8
Dimension - Hole Size inch	0.69
Dimension - Hole Size mm	17.5 mm
Dimension - Length Overall inch	4.37 in
Dimension - Outside Diameter inch	0.63 in
Dimension - Pad Width inch	23.6 in
Dimension - Strip Length inch	0.87 in
Dimension - Stud Size fraction	5/8
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor - Material	COPPER
Conductor Size	95 mm <sup>2</sup>
Conductor Type	CLASS 2

## Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	10
-----------------------	----

## Product Assets

[3D Models - YAV952M16\\_MODEL-STEP](#)  
[3D Models - YAV952M16\\_MODEL-PDF](#)  
[3D Models - YAV952M16\\_MODEL-IGES](#)  
[Sales Drawings - 50025887](#)