



Compression Terminal

By Burndy
Catalog # [YAZ254TC38E1G1](#)



Copper Compression Terminal; 4-Hole Pad; 3/8" Stud.

Application

Wire Termination

General

Color Code	Pink
Connector Type	LONG BARREL
Die Index	12
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810649183
UPC 12 Digit	7818106491833

Dimensions

Dimension - B Length inch	1.38
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - E Spacing between Holes fraction	1.13
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	101
Dimension - Length Overall inch	3.96
Dimension - N inch	0.31
Dimension - Outside Diameter inch	0.51
Dimension - Pad Width inch	1.63
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size fraction	3/8
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	100 Navy
Conductor - Copper Str Size	1/0 AWG
Conductor - Material	COPPER
Conductor Size	1/0 AWG
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	20

Product Assets

- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50025312](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

