



## YAZ262N, Cu Compression, 2-Hole, 1/2" Stud, 1-3/4" Spacing, Long Barrel, 2/0 AWG

By Burndy  
Catalog # [YAZ262N](#)



2/0 AWG CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Black Color Code, 13 Die Index.

### Application

Wire Termination

### General

Catalog Number	YAZ262N
Color Code	Black
Connector Type	LONG BARREL
Die Index	13
EU RoHS Indicator	Yes
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810208571
UPC 12 Digit	7818102085711

### Dimensions

Dimension - B Length fraction	1-1/2
Dimension - B Length inch	1.5
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - E Spacing between Holes fraction	1-3/4
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	126
Dimension - Length Overall inch	4.95
Dimension - N inch	0.62
Dimension - Outside Diameter inch	0.56
Dimension - Pad Width inch	0.83
Dimension - Strip Length inch	1-9/16
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.64
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

### Conductor Related

Conductor - Copper Str Navy Size	125 Navy
Conductor - Copper Str Size	2/0 AWG
Conductor - Material	COPPER
Conductor Size	2/0 AWG
Conductor Type	CODE

## Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	10
Minimum Pack Quantity	1

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - se2119372](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

