



YAZ292TC38, Cu Compression, 2-Hole, 3/8" Stud, 1" Spacing, Long Barrel, 250 kcmil

By Burndy
Catalog # [YAZ292TC38](#)



250 kcmil CU, Two Hole, 3/8 Stud Size, 1 Hole Spacing, Long Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Yellow Color Code, 16 Die Index.

Application

Wire Termination

General

Catalog Number	YAZ292TC38
Color Code	Yellow
Connector Type	LONG BARREL
Die Index	16
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none">ChamferedSkived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Yes
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810065440
UPC 12 Digit	7818100654400

Dimensions

Dimension - B Length inch	1.62 in
Dimension - Bolt Hole Size inch	0.4 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	101 mm
Dimension - Length Overall inch	3.99 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	1.10 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size fraction	3/8

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	250 (61) Navy
Conductor - Copper Str Navy Size Range	250 (61) Navy
Conductor - Copper Str Size	250 KCMIL
Conductor - Material	COPPER
Conductor Size	250 KCMIL
Conductor Type	CODE

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1

Product Assets

[3D Models - YAZ292TC38_MODEL-PDF](#)
[3D Models - YAZ292TC38_MODEL-IGES](#)
[3D Models - YAZ292TC38_MODEL-STEP](#)
[Catalogs - Full Line BURNDY Catalog](#)
[Catalogs - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
[Sales Drawings - se21191529](#)
[Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch	3/8
Dimension - Z (inch)	1.43 in
Physical Attribute - Tongue Angle	Straight



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAZ292TC38-SPEC-EN | REV 6/2024