



YAZ2C2NTC38, Compression Terminal, 2 AWG Cu, 2-Hole, 3/8" Stud, 1-3/4" Spacing, Long Barrel

By Burndy
Catalog # [YAZ2C2NTC38](#)



2 AWG CU, Two Hole, 3/8 Stud Size, 1-3/4 Hole Spacing, Long Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Brown Color Code, 10 Die Index.

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

General

Catalog Number	YAZ2C2NTC38
Color Code	Brown
Connector Type	LONG BARREL
Die Index	10
EU RoHS Indicator	Yes
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Yes
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810227756
UPC 14 Digit GTIN	00781810227756

Dimensions

Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.4 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm

Dimension - L Length Overall mm	106 mm
Dimension - Length Overall inch	4.16 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.60 in
Dimension - Strip Length inch	1-5/16
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8
Dimension - Z (inch)	2.18 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Size	2 AWG
Conductor - Material	COPPER
Conductor Size	2 AWG
Conductor Type	CODE

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	24000

Product Assets

- Catalogs - BURNDY Master Catalog - Section C - Compression Connections
- Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog

- Customer Notices - Prop 65 Notice
- Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions
- Installation Manuals - Medium & Large HYDENT Copper & Aluminum Terminal Crimp Instructions with 750 Series 12-Ton Tool
- Interactive Catalog - BURNDY Full-Line Digital Catalog
- Sales Drawings - se21191517
- Specifications - YAZ2C2NTC38
- Video - HYDENT Compression Terminal Overview Video

