



YAZ342NTCFXB, Compression Terminal, 373.3 kcmil 925/24, 350 kcmil, Cu, 2-Hole, 1/2" Stud, Long Barrel

By Burndy
Catalog # YAZ342NTCFXB



Cu compression long barrel flex conductor, 2 holes/W/ insp window, 373.3 kcmil(925/24), 350 kcmil nom, 1/2" stud, Blue, 19 index.

Application

Wire Termination

General

Catalog Number	YAZ342NTCFXB
Connector Type	LONG BARREL
Construction Material - Main	Copper
Die Index	19
EU RoHS Indicator	Yes
Feature - Barrel Style	<ul style="list-style-type: none">BelledSkived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810238660
UPC 12 Digit	7818102386600

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.48 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.56
Dimension - Hole Size mm	14 mm
Dimension - Inside Diameter inch	0.83 in
Dimension - L Length Overall mm	159 mm
Dimension - Length Overall inch	6.27 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	3/8
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.65 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	373 KCMIL
Conductor - Copper DLO Size	373 kcmil
Range	
Conductor - Copper Flex G Size	350 KCMIL
Conductor - Copper Flex G Size	350 kcmil
Range	
Conductor - Copper Flex H Size	350 KCMIL
Conductor - Copper Flex H Size	350 kcmil
Range	
Conductor - Copper Flex I Size	350 KCMIL
Conductor - Copper Flex I Size	350 kcmil
Range	
Conductor - Copper Flex K Size	350 KCMIL
Conductor - Copper Flex K Size	350 kcmil
Range	
Conductor - Copper Flex M	350 KCMIL
Size	
Conductor - Copper Flex M	350 kcmil
Size Range	
Conductor - Copper Str Size	350 KCMIL
Conductor - Copper Str Size	350 kcmil
Range	
Conductor - Material	COPPER
Conductor Size	350 kcmil
Conductor Type	FLEX
Wire Size	350 KCMIL

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	6
Minimum Pack Quantity	1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50015619](#)
- [Specifications - YAZ342NTCFXB](#)
- [Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand