



# Compression Terminal

By Burndy  
Catalog # [YAZ41TC1290](#)

850 kcmil CU, One Hole, 1/2 Stud Size, Long Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Gold Color Code, 26 Die Index.



## Application

Wire Termination

## General

Color Code	Gold
Connector Type	LONG BARREL
Die Index	26
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810240786
UPC 12 Digit	7818102407866

## Dimensions

Dimension - B Length fraction	2-15/16 in
Dimension - B Length inch	2.94 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Height inch	4.43 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	1.98 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.38 in
Dimension - Pad Width inch	2.01 in
Dimension - Strip Length inch	3
Dimension - Stud Size fraction	1/2
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	90 Degree

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	850 KCMIL
Conductor - Material	COPPER
Conductor Size	850 KCMIL
Conductor Type	CODE

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Sales Drawings - SE..212356-33](#)

[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-YAZ4ITC1290-SPEC-EN | REV 8/2023