



YAZ442NT38FX, Cu Compression, 2-Hole, 3/8" Stud, 1" Spacing, Long Barrel, Narrow Tongue, 750 kcmil G, H, 777 DLO

By Burndy
Catalog # YAZ442NT38FX



750 kcmil G,H,777 DLO CU, Two Hole, 3/8 Stud Size, 1 Hole Spacing, Long Barrel, Inspection Window, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Yellow Color Code, L115 Die Index.

Application

Wire Termination

General

Catalog Number	YAZ442NT38FX
Color Code	Yellow
Connector Type	LONG BARREL
Die Index	L115
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YAZ-2-NTFX, Long Barrel Narrow Tongue
UPC	781810166178

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3.00 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Bolt Size inch	0.38
Dimension - Diameter Min Size inch	2.03 in
Dimension - Hole Size fraction	3/8
Dimension - Hole Size inch	0.41
Dimension - Hole Size mm	10.4 mm
Dimension - L Length Overall mm	155 mm
Dimension - Length Overall inch	6.09 in
Dimension - Length Side B inch	6.08 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	3-1/16
Dimension - Stud Size fraction	3/8
Dimension - Stud Size inch	3/8 in
Dimension - Z (inch)	0.53 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper DLO Size	777 KCMIL
Conductor - Copper DLO Size	777 kcmil
Range	
Conductor - Copper Flex G Size	750 KCMIL
Conductor - Copper Flex G Size	750 kcmil
Range	
Conductor - Copper Flex H Size	750 KCMIL
Conductor - Copper Flex H Size	750 kcmil
Range	
Conductor - Copper Flex I Size	750 KCMIL
Conductor - Copper Flex I Size	750 kcmil
Range	
Conductor - Copper Flex K Size	750
Conductor - Copper Flex M	750
Size	
Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Str Size	750 kcmil
Range	
Conductor - Material	COPPER
Conductor Size	750 KCMIL
Conductor Type	FLEX
Wire Size	750 KCMIL

Certifications And Compliance

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	1800

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Installation Manuals - Copper Flex Long Terminals Tooling and Installation Instructions](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_YAL2NNTFX_Lineart](#)
[Sales Drawings - 30003952](#)
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-YAZ442NT38FX-SPEC-EN | REV 8/2024