



Compression Terminal

By Burndy
Catalog # [YAZ46TC1245](#)

1500 kcmil CU, Two Hole, 1/2 Stud Size, 1-3/4 Hole Spacing, Long Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Green Color Code, 31 Die Index.



Application

Wire Termination

General

Color Code	Green
Connector Type	LONG BARREL
Die Index	31
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810240922
UPC 12 Digit	7818102409222

Dimensions

Dimension - B Length fraction	3-3/16 in
Dimension - B Length inch	3.19 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Height inch	4.57 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	131 mm
Dimension - Length Overall inch	5.15 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.84 in
Dimension - Pad Width inch	2.69 in
Dimension - Strip Length inch	3-1/4
Dimension - Stud Size fraction	1/2
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

Conductor Related

Conductor - Copper Str Size	1500 KCMIL
Conductor - Material	COPPER
Conductor Size	1500 KCMIL
Conductor Type	CODE

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Sales Drawings - SE..212356-37](#)

[Video - HYDENT Compression Terminal Overview Video](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAZ46TC1245-SPEC-EN | REV 8/2023