



**YAZ486TC1245, Compression  
Terminal, 2500 kcmil Cu, 1-Hole,  
1/2" Stud, Long Barrel, 45 Degree**

By Burndy  
Catalog # [YAZ486TC1245](#)

CULUG-2500KCM-LNG W/PORT.



## Application

Wire Termination

## General

Catalog Number	YAZ486TC1245
Connector Type	LONG BARREL
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Finish Type	Tin-Plated
Material	COPPER
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810241097
UPC 12 Digit	7818102410977

## Dimensions

Dimension - B Length fraction	4-11/16 in
Dimension - B Length inch	4.69 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5
Dimension - Height inch	6.28 in
Dimension - Hole Size fraction	1/2
Dimension - Hole Size inch	0.53
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	170 mm
Dimension - Length Overall inch	6.71 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	2.38 in
Dimension - Pad Width inch	3.46 in
Dimension - Strip Length inch	4-3/4
Dimension - Stud Size fraction	1/2
Dimension - Z (inch)	0.55 in
Physical Attribute - Tongue Angle	45 Degree

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	35 kV

## Conductor Related

Conductor - Copper Str Size	2500 KCMIL
Conductor - Material	COPPER
Conductor Size	2500 KCMIL
Conductor Type	CODE

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - SE..212356-40](#)  
[Specifications - YAZ486TC1245](#)  
[Video - HYDENT Compression Terminal Overview Video](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-YAZ486TC1245-SPEC-EN | REV 8/2024