



YAZ4C2TC10E2, Compression Terminal, 4 AWG Cu, 2-Hole, #10 Stud, 3/4" Spacing, Long Barrel

By Burndy
Catalog # [YAZ4C2TC10E2](#)

4 AWG, CU, 2 Hole, #10 Stud, 3/4 IN Spacing, Long Barrel, Inspection Window

Features

- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the strands
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors are clearly marked with stamping and barrel color coding

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Conductor - Copper Str Size	4 AWG
Conductor Size	4 AWG
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor Type	CODE

Configuration

Physical Attribute - Number of Holes	2
Number of Pad Holes	2
Connector Type	LONG BARREL

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Dimension - Pad Width inch	0.50 in
Package Height	0.000 in
Dimension - Hole Size fraction	#10
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	68 mm
Dimension - Outside Diameter inch	0.34 in
Dimension - Hole Size mm	5.3 mm
Dimension - Hole Size inch	0.21
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size inch	#10
Dimension - Stud Size fraction	#10
Dimension - Bolt Hole Size inch	0.20 in
Dimension - Bolt Size fraction	#8-#10
Physical Attribute - Tongue Angle	Straight
Dimension - B Length fraction	1-1/8 in
Dimension - Z inch	0.27 in
Dimension - B Length inch	1.12 in
Dimension - N inch	0.25 in
Dimension - Bolt Size inch	0.21
Dimension - Length Overall inch	2.67 in

General

Trade Name	HYLUG™
Die Index	8
Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Y
Color Code	Gray
Physical Attribute - Tongue Type	Standard
UPC	781810227633
Type	Long Barrel, Skive, Tin Plated
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810227633
UPC 14 Digit GTIN	00781810227633

Logistics



Minimum Pack Quantity	50
Carton Quantity	50

Product Assets

- Catalog [English]
- Installation Manual [English]
- Installation Manual [French, English]



A Hubbell brand