

Compression Terminal

By Burndy
Catalog # [YAZ4C2TC38](#)

4 AWG CU, Two Hole, 3/8 Stud Size, 1 Hole Spacing, Long Barrel, Inspection Window Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Gray Color Code, 8 or 346 Die Index.



Application

Wire Termination

General

| | |
|--------------------------------------|--------------------------------|
| Catalog Number | YAZ4C2TC38 |
| Color Code | Gray |
| Connector Type | LONG BARREL |
| Die Index | 8 |
| EU RoHS Indicator | Yes |
| Feature - Barrel Style | Skived |
| Feature - Barrel Type | Long |
| Finish Type | Tin-Plated |
| Material | COPPER |
| Physical Attribute - Number of Holes | 2 |
| Physical Attribute - Tongue Type | Standard |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Sub Brand | HYLUG |
| Trade Name | HYLUG™ |
| Type | Long Barrel, Skive, Tin Plated |
| UPC | 781810227657 |
| UPC 12 Digit | 7818102276577 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 1-1/8 in |
| Dimension - B Length inch | 1.12 in |
| Dimension - Bolt Hole Size inch | 0.39 in |
| Dimension - Bolt Size fraction | 3/8 |
| Dimension - Bolt Size inch | 0.38 |
| Dimension - Hole Size fraction | 3/8 |
| Dimension - Hole Size inch | 0.41 |
| Dimension - Hole Size mm | 10.4 mm |
| Dimension - L Length Overall mm | 82 mm |
| Dimension - Length Overall inch | 3.23 in |
| Dimension - N inch | 0.41 in |
| Dimension - Outside Diameter inch | 0.34 in |
| Dimension - Pad Width inch | 0.58 in |
| Dimension - Strip Length inch | 1-3/16 |
| Dimension - Stud Size fraction | 3/8 |
| Dimension - Stud Size inch | 0.375 in |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 35000 |
| Voltage Rating | 35 kV |

Conductor Related

| | |
|----------------------------------|--------------|
| Conductor - Copper Str Navy Size | 40 (19) Navy |
| Conductor - Copper Str Size | 4 AWG |
| Conductor - Material | COPPER |
| Conductor Size | 4 AWG |
| Conductor Type | CODE |

Certifications And Compliance

| | |
|------------------------------------|--------------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Carton Quantity | 50 |
| Minimum Pack Quantity | 1 |

Product Assets

- [Catalogs - Full Line BURNDY Catalog](#)
- [Catalogs - Section C - Compression Connections](#)
- [Customer Notices - Prop 65 Notice](#)
- [Installation Manuals - Copper Code Long Terminals Tooling and Installation Instructions](#)
- [Sales Drawings - SE211915-10](#)
- [Video - HYDENT Compression Terminal Overview Video](#)

Dimension - Stud Size inch 3/8
Dimension - Z (inch) 0.43 in
Physical Attribute - Tongue Angle Straight



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-YAZ4C2TC38-SPEC-EN | REV 6/2024